



SOLID GLASS MICROSPHERES

Langfang Olan Glass Beads Co., Ltd

1014, B-2, New World Centre, Aimin East Road, Langfang City, Hebei, China

Phone :+86 151 0066 3145 Email: info@olanbeads.com Web: www.olanbeads.com

TECHNICAL DATA SHEET

技术参数

Product Name 品名: 玻璃微珠/Glass Microspheres

Main Component 成分: 硅酸铝钙钠/Aluminum Calcium Sodium Silicate

Model 规格: MC80A

Testing Items 检测项目	Control Standard 控制标准	Test Method 检测方法
Appearance 外观	White and Good fluidity 白色无板结、流动性好	Powder flow test 粉末流动测试
Moisture Content 水分 (%)	≤ 0.50	Moisture Meter 水分测定仪
粒径(典型值) Particle Size(Typical Value) (μm)	D90: 80 ± 5	Laser particle size analyzer 马尔文激光粒度分析仪
	D50: 35 ± 5	
Specific Gravity 真密度 (g/cm^3)	2.55 ± 0.15	True density detector 麦克默瑞提克真密度检测仪
PH	6.8~7.8	PH 测试仪

产品保质期及存储条件/Product Shelf Life and Storage Conditions:

保质期/Shelf Life	存储条件/Storage Conditions
自生产之日起 24 个月 24 Months From Date of Production	室内相对干燥、通风环境存放，原始未开封的包装。 Storage in a dry and ventilated environment, with original sealed packaging.

您购买和使用澳澜玻璃微珠，是对我们最大的信任和支持，我们将一如既往保证每一批产品质量。

Your purchase and use of OLAN's glass microspheres is the best trust and support. We will continue to ensure the quality of each batch of products.